


MISALI


Mounting examples



Type E

2 Type

- E** For one clamping bolt
- Z** For two clamping bolts



Type Z

1

for power clamps Size	s	d ₁	d ₂ ^{H8/h6}	d ₃	h	l ₁	l ₂	l ₃	l ₄	m ₁	m ₂	m ₃	m ₄
20	32	M 8	7	M 5	10	98,5	15	30	8	34	53	22	17
32	42	M 10	9	M 6	14	140	19	40	8,5	51	74,4	30	23
40	52	M 12	11	M 8	16	168	22	50	12,5	62	88,5	37	30
50	62	M 12	13	M 10	18	192,5	22	60	12,5	71,5	102	44	40

Specification

- Steel C45
Chemically nickel plated **NC**
- Socket cap screws DIN 912,
Centering guide bushings
Steel, blackened
- *ISO Fundamental Tolerances* → Page 2151
- RoHS

3

Information

Static holders GN 869.1 have been designed for use with power clamps GN 865.

Static holders for two clamping bolts (Type Z) are preferably used in such applications where absolutely rigid clamping of a sheet metal component is essential. For the same purpose ball point screws GN 605 with serrated ball pads are ideally suited.

Socket cap screws and centering guide bushings are included.

see also...

- *Ball Point Screws GN 605* → Page 1052

How to order

GN 869.1-52-E-NC

1	s
2	Type
3	Finish