



2

3

for swing clamps Size	d ₁	m	a	b ₁	b ₂	b ₃	d ₂	d ₃	h ₁	h ₂	Length l
25	14	50	20	6,5	11,3	18	M 6	8,5	16	6,5	64,6
32 / 40	16	65	25	8,5	14,5	20	M 8	8,5	18	9	82,2
50 / 63	20	85	30	10,5	17,5	25	M 10	10,5	23	10	106,2

Specification

1

4

- Aluminum **AL**
- hard anodized wear-resistant surface **HE**
- Flanged washers
Steel, zinc plated, blue passivated
- Socket cap screw DIN 912
Steel, zinc plated, blue passivated
- Washer ISO 7092
Steel, zinc plated, blue passivated
- RoHS

Accessory

- Toggle clamp spindle assemblies GN 708.1
→ Page 31

Information

Clamping arms GN 875.2 with slotted hole designed as accessories to swing clamps GN 875 / GN 876. The slotted hole allows arbitrary positioning of application-specific pressing elements in connection with the two flanged washers.

The angle orientation of the clamping arm can be set arbitrarily during mounting on the swing clamp. When tightening the screw, the piston rod must not experience any torque. The clamping arm must therefore be held to prevent twisting.

Included are a socket cap screw DIN 912 and a washer ISO 7092 for fastening to the swing clamp as well as two flanged washers for fastening the clamping bolts.

see also...

- Swing clamps GN 875 (pneumatic, in block version) → Page 58
- Swing clamps GN 876 (pneumatic, with screw-in thread) → Page 60

How to order

1	Material
2	d ₁
3	m
4	Finish

GN875.2-AL-16-65-HE