



3 Type

EG single, friction bearing

DG double, friction bearing

1

2

d₁	d₂ H8 Bore	l₁ Type EG	l₂ Type DG	l₃	l₄	t +1 max. assembly length of the shaft	max. torque in Nm
13	B 8	42	60	21	18	12	2
16	B 10	52	74	26	22	15	3
20	B 12	62	88	31	26	18	6
25	B 16	74	104	37	30	22	12
32	B 20	86	124	43	38	25	24

Specification

- Steel
 - not hardened
 - blackened
- Cross holes GN 110.1 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- RoHS

Information

Universal joints GN 9080 are a simple and very competitively priced variant.

They can only be used for applications with low revolutions. Typical applications are all types of manual operations such as the adjustment of louvers.

How to order

GN 9080-20-B12-EG

1 d₁
2 d₂
3 Type