



3 Type

- A** Without sealing ring
- AC** With sealing ring in copper
- AA** With sealing ring in aluminum
- AN** With sealing ring in stainless steel

2

d ₁			d ₂ h14	d ₃	d ₄ Sealing Outside diameter	l ₁ ±0,2	l ₂ ±0,5	l ₃	s	A/F
M 8 x 1	M 8 x 1	-	14	8,3	11,5	8	9	6 -1	1	10
M 10 x 1	M 10 x 1	-	14	10,3	13,5	8	9	6	1	10
-	-	G 1/8	14	10	13,5	8	9	6	1	10
M 12 x 1,5	M 12 x 1,5	-	17	12,3	16	12	9	6	1,5	13
-	-	G 1/4	18	13,4	18	12	9	6	1,5	13
M 14 x 1,5	M 14 x 1,5	-	19	14,3	18	12	9	6	1,5	13
M 16 x 1,5	M 16 x 1,5	-	21	16,3	20	12	9	6	1,5	17
-	-	G 3/8	22	17	21	12	9	6	1,5	17
M 18 x 1,5	M 18 x 1,5	-	23	18,3	22	12	12	8	1,5	17
M 20 x 1,5	M 20 x 1,5	-	25	20,3	24	14	12	8	1,5	19
-	-	G 1/2	26	21,3	26	14	12	8	1,5	19
M 22 x 1,5	M 22 x 1,5	-	27	22,3	27	14	12	8	1,5	19
M 24 x 1,5	M 24 x 1,5	-	29	24,3	29	14	13	9	2	22
M 26 x 1,5	-	-	31	26,3	31	16	14	10	2	24
M 27 x 2	-	-	32	27,3	32	16	14	10	2	24
-	-	G 3/4	32	26,7	32	16	14	10	2	24
M 30 x 1,5	-	-	36	30,3	36	16	14	10	2	24
M 33 x 2	-	-	39	33,3	39	16	16	11	2	27
-	-	G 1	39	33,5	39	16	16	11	2	27
M 42 x 2	-	-	49	42,3	49	16	17	12	2	30
-	-	G 1 1/4	49	42,2	49	16	17	12	2	30
M 48 x 2	-	-	55	48,3	55	16	17	12	2	30
-	-	G 1 1/2	55	48,1	55	16	17	12	2	30

Specification

Threaded plug

- Steel **ST**
- Zinc plated, blue passivated
- Property class 5.8
- Stainless steel AISI 316 / AISI 316Ti **A4**

Sealing ring DIN 7603

for type AC / AA / AN

RoHS

Technical Information

ISO Fundamental Tolerances	QVX
Strength Values of Screws	QVX
Stainless Steel Characteristics	QVX

Threaded plugs DIN 910 are used, for example, on filling, drain or inspection openings of gear boxes and hydraulic tanks.

see also...

	Page
GN 745 Threaded Plugs (Plastic)	QVX
GN 749 Threaded Plugs (with Rubber Sealing)	QVX
DIN 908 Threaded Plugs (with Internal Hex)	QVX

Accessory

DIN 7603 Sealing Rings	QVX
-------------------------------	-----

How to order

1 Material	
2 d ₁	
3 Type	

DIN 910-A4-M16x1,5-AN

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

