


- 3 Type**
- H** Clamping screw with adjustable handle
 - S** Clamping screw with internal hex



1 d_1	2 d_2 H7			d_3	b	m	l_1	l_2 max. Type H	l_3 max. Type S
40	B 8	B 10	-	4,3	16	28	30	50	27
50	B 8	B 10	B 12	5,3	16	36	30	56	32
60	B 10	B 12	-	5,3	16	44	30	61	36

Specification

Clamping Element

Aluminum
Anodized, black

ELS

Wedge

Brass

Adjustable hand lever for type H

- Zinc die casting
- Powder coated
Black, RAL 9005, textured finish
- With setting screw
Stainless steel AISI 303

Clamping screw for type S

Stainless steel AISI 303

RoHS

Accessory

GN 711.1 Indicator Arrows (self-adhesive)

Page

QVX

Clamping elements GN 826 are normally used in connection with control knobs and smaller handwheels.

Spindles can so be clamped gently and easily and without much construction and installation effort. The clamping wedge stiffens the spindle, e.g., to prevent maladjustments caused by vibrations or to secure the spindle after adjustment.

This clamping element can also be used to store the spindle

The clamping element may be mounted such that the clamping lever / the clamping screw is positioned either on the left or the right hand side.

Indicator arrows which can be attached to the circumference of the clamping element are found under GN 711.1.

Technical Information

ISO Fundamental Tolerances

Stainless Steel Characteristics

Page

QVX

QVX

How to order

GN 826-40-B10-H-ELS

- 1** d_1
- 2** d_2
- 3** Type
- 4** Finish

