



1

2

d <sub>1</sub>	d <sub>2</sub> H9	b <sub>1</sub> <sup>-0,05 -0,15</sup>	b <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub> Gear lever handle	Length l	r <sub>1</sub>	r <sub>2</sub>	r <sub>3</sub>	r <sub>4</sub>	s	t min.
24	B 8	13	11	M 6	8	28	12	13,32	14,64	15,3	3,3	9
30	B 10	15	13	M 8	10	32	15	16,65	18,3	19,12	4,1	12
35	B 12	17	15	M 10	12	36	17,5	19,42	21,34	22,31	4,8	15

**Specification**

**Steel**

- Sintered
- Case-hardened  
EHT 0,2 to 0,4 mm
- Plain

RoHS

Hubs with eccentric cam GN 919 are used for adjusting and clamping operations. As a rule these are fitted with a gear lever handle GN 310.

The cam offers the advantage that the clamping force remains constant in every position of its travel. In addition the cam is self locking.

Cylinder head shoulder bolts GN 732.1 can be used as bearing pins.

**see also...**

	Page
<b>GN 732.1</b> Cylinder Head Shoulder Bolts	QVX
<b>GN 918</b> Eccentric Cams (rotary clamping ring)	QVX

**Technical Information**

ISO Fundamental Tolerances	QVX
----------------------------	-----

**Accessory**

<b>GN 310</b> Gear Lever Handles	QVX
<b>GN 310</b> Gear Lever Handles	QVX

**How to order**

**GN 919-35-B12**

1	d <sub>1</sub>
2	d <sub>2</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

