



**2** Type  
AS Sheet metal body



Size	FH in N Holding capacity	a	b	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub> ≈	h <sub>2</sub>	l <sub>1</sub> ≈
120	3600	17	48	12	M 6	5,5	111	31	130
300	7200	20	58	14	M 8	6,5	140	36	167

Size	l <sub>2</sub> ≈	l <sub>3</sub> ≈	l <sub>4</sub> ≈	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	A/F	t	w Stroke
120	121	40	30	34	30	17	24	12	20
300	155	57	45	50	34	18	27	16	34

### Specification

- Parts in sheet metal  
Case-hardened steel C10  
zinc plated, blue passivated
- Plunger Steel St 37  
zinc plated, blue passivated
- Plunger guide bushing brass  
zinc plated, blue passivated
- All moving parts  
lubricated with special grease
- Hand grip  
High quality, oil resistant, red plastic
- RoHS

### Accessory

- Spindle assemblies → Page 585 ff.

### Information

see also...

- General information for toggle clamps → Page 500

How to order

**GN 841-120-AS**

**1** Size

**2** Type

