



Mounting examples



Type E



Type Z



Type

- E For one clamping bolt
- Z For two clamping bolts

For power clamps Size	<sup>1</sup> b -0,2	<sup>2</sup> d <sub>1</sub>	d <sub>2</sub> <sup>H8/h6</sup>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	m <sub>4</sub>	m <sub>5</sub>
20	32	M 8	7	M 5	10	10	38	13	37	7,5	22	17	15	31,5	17
32	42	M 10	9	M 6	12	12	54,5	17	48,5	10	30	25	17,5	45,9	23
40	52	M 12	11	M 8	14	14	63	20	61	13,5	37	30	23,5	53	30
50	62	M 12	13	M 10	16	16	73,5	20	83,5	13,5	44	47	27	63,5	40

**Specification**

- Steel C45  
Chemically nickel plated **NC**
- Socket cap screws DIN 912, centering guide bushings  
Steel, blackened
- ISO Fundamental Tolerances → Page 2151
- RoHS

**Information**

Static holders GN 867.1 have been designed for use with power clamps GN 864.

Static holders with two clamping bolts (Type Z) are preferably used for rigid clamping of sheet metal components. For the same purpose ball point screws GN 605 with serrated ball pads are ideally suited.

Static holders are made from a single piece (b = 32) or from two connected pieces (b = 42...62).

Socket cap screws and centering guide bushings are included.

see also...

- Power Clamps GN 864 → Page 822
- Ball Point Screws GN 605 → Page 1052

How to order	1 b
<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup> <b>GN867.1-42-M10-Z-NC</b>	2 d <sub>1</sub>
	3 Type
	4 Finish