



- 2 Bore code**
 - B** Without keyway
 - K** With keyway DIN 6885-1 P9
- 4 Type**
 - A** Without handle
 - R** With revolving handle

1 d_1	3 d_2 H7 Bore	d_3	d_4	b	h	l_1	$l_2 \approx$	$l_3 \approx$	r	\emptyset Handle GN 798.2	\emptyset Handle GN 599.5	Recommended countersunk washer
50	6	8	20	13	13	7	16	26	20	16	-	GN 184-12
63	8	10	23	17	13	7	16	26	20	20,5	-	GN 184-16
80	10	12	26	17	13	7	16	26	43,5	27,5	16	GN 184-16
100	10	12	28	22	14	9,5	17	30	58	36	18	GN 184-20
125	12	14	31	22	15	11	18	33	61	45,5	22	GN 184-20
140	14	16	36	28,5	16,5	13	19	36	76	52	24	GN 184-25
160	14	16	36	28,5	18	14,5	20	39	76	61	24	GN 184-25
200	18	20	42	36	20,5	16	24	45	85	77,5	25	GN 184-32

Specification

Wheel body

- Aluminum die casting
- Hub machined
- Rim turned
- Radial and axial runout < 0.4
- Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish

- SW**
- SR**

Cover

- Plastic, Polyamide (PA)
- Light grey

Revolving handle GN 798.2

- Plastic, Polyamide (PA)
- Black, matte finish
- Spindle steel
- Zinc plated, blue passivated

Revolving cylindrical handle GN 599.5

- Plastic, Polyamide (PA)
- Black, matte finish
- Spindle stainless steel AISI 303

RoHS

Disk handwheels GN 923 are distinguished by modern design.

The removable plastic cover shrouds the fixing components such as countersunk washers and protruding or recessed shafts.

see also...

GN 321 Disk Handwheels (Aluminum, Rim Polished)	Page QVX
--	--------------------

Technical Information

Keyway P9 DIN 6885-1	QVX
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX

Accessory

GN 184 Countersunk Washers (for axial fixation)	QVX
--	-----

How to order

1 d_1
2 Bore code
3 d_2
4 Type
5 Color

GN 923-140-B14-R-SW