




Application example



ELESA original design NCD



A/F	d ₀ for DIN nuts or screws	d ₁	d ₂	h ₁	h ₂	h ₃	t ≈ max.
7	M 4	9	6,9	7,8	3,5	6,5	5
8	M 5	10,9	7,9	10,4	6	9,3	7
10	M 6	12,9	9,8	12,4	7	11,4	9
13	M 8	16,3	12,8	15	8,5	14	12
17	M 10	20,3	16,7	19,1	9	17,2	14
19	M 12	22,6	18,7	20	10,1	17,9	15
22	M 14	27	21,7	23,5	11,5	22	19
24	M 16	29,2	23,7	26	14,6	24	20
30	M 20	35,7	29,8	32,8	17,9	30,2	26
36	M 24	44	35,8	40	20	37,6	33
46	M 30	55,1	45,8	50,2	24,5	47,7	42

Specification

- Plastic
Technopolymer (Polyethylene PE)
- temperature resistant up to 80 °C
- black, RAL 9005, matte ● SW
- Plastic characteristics → Page 1483
- RoHS

On request

- Cover caps with other wrench sizes
- Plastic chrome plated



Information

Cover caps GN 934.1 are designed for hexagon nut and screw sizes according to DIN 933 / DIN 934.

They protect from dirt and corrosion and attractively cover projecting screws and nuts. Moreover, they reduce the danger of injury from sharp edges.

The cover caps can be mounted by hand or using a soft-head hammer.

How to order

GN934.1-10-SW

1 A/F

2 Color

