


 Inox  
Stainless  
Steel

**2 Bore code**
**B** Without keyway

**K** With keyway DIN 6885-1 P9

**4 Type**
**A** Without handle

**D** With revolving handle

1

3

| d <sub>1</sub> | d <sub>2</sub> H8<br>Bore |    | b  | d <sub>3</sub> | l <sub>1</sub> | l <sub>2</sub> ≈ | l <sub>3</sub> ≈ | r  | Ø<br>Handle | No. of<br>spokes |
|----------------|---------------------------|----|----|----------------|----------------|------------------|------------------|----|-------------|------------------|
| 100            | 10                        | 12 | 7  | 20             | 15             | 27,5             | 45               | 44 | 18          | 3                |
| 125            | 12                        | 14 | 9  | 24             | 16             | 28,5             | 55               | 55 | 21          | 3                |
| 140            | 14                        | 16 | 10 | 28             | 18             | 30,5             | 70,5             | 62 | 23          | 3                |
| 160            | 14                        | 16 | 11 | 31             | 20             | 35,5             | 70,5             | 71 | 23          | 3                |
| 200            | 18                        | 20 | 14 | 36             | 23             | 39               | 70,5             | 90 | 23          | 3                |

**Specification**
**Wheel body**

Stainless steel precision casting AISI CF-8

- Hub machined
- Rim turned
- Matte shot-blasted

**Revolving handle** similar to GN 598.1

Plastic, Phenolic resin (PF)

- Black, shiny finish
- Spindle
- Stainless steel AISI 304

RoHS

The design of handwheels GN 949 complies with the requirements of hygiene standards.

The revolving handles are made of phenolic resin which, in general, provides good resistance to the impact of chemical agents.

**Technical Information**

Keyways P9 DIN 6885-1

Cross holes GN 110

ISO Fundamental Tolerances

Stainless Steel Characteristics

**Page**

QVX

QVX

QVX

QVX

**Accessory**
**GN 184.5** Countersunk Washers (for Axial Fastening)

QVX

**How to order**

  
**GN 949-125-B12-A**
**1** d<sub>1</sub>
**2** Bore code

**3** d<sub>2</sub>
**4** Type