



ELESA Original design RB51/RB52/RB50



<sup>1</sup> d <sub>1</sub> f7	<sup>2</sup> d <sub>2</sub> H7 Bore							<sup>3</sup> l <sub>1</sub>	d <sub>3</sub>	l <sub>2</sub>	for position indicators
10	B 6	B 8	-	-	-	-	-	20	3,2	2,5	GN 955
14	B 6	B 8	B 10	B 12	-	-	-	20	4,25	3,5	GN 954 / GN 9054
20	B 6	B 8	B 10	B 12	B 14	B 15	B 16	20	5,5	4,5	GN 953 / GN 9053

**Specification**

- Steel blackened —
- Stainless Steel AISI 304 **NI**
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- RoHS



**Information**

With the help of adapter bushings GN 952.1 position indicators can be adapted to accept different smaller spindle diameters.

The adapter bushings are supplied with a set screw.

see also...

- Position indicators GN 953 → Page 296
- Position indicators GN 954 → Page 298
- Position indicators GN 955 → Page 300
- Position indicators GN 9053 → Page 302
- Position indicators GN 9054 → Page 304

How to order (Steel)

<sup>1</sup> <sup>2</sup> <sup>3</sup>  
**GN 952.1 - 14 - B12 - 20**

<sup>1</sup>	d <sub>1</sub>
<sup>2</sup>	d <sub>2</sub>
<sup>3</sup>	l <sub>1</sub>

How to order (Stainless Steel)

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**GN 952.1 - 10 - B8 - 20 - NI**

<sup>1</sup>	d <sub>1</sub>
<sup>2</sup>	d <sub>2</sub>
<sup>3</sup>	l <sub>1</sub>
<sup>4</sup>	Material