



1 2 3

d ₁	d ₂	l ₁				l ₂	l ₃ ≈	m	A/F
15	M 6	26	36	46	-	7,6	3,6	5,2	3
15	M 8	20	35	45	58	7,6	2,5	6,8	4
18	M 8	20	35	45	58	9,2	4,2	6,8	4
18	M 10	34	44	57	74	9,2	3,4	8,4	5
21	M 8	20	35	45	58	10	5	6,8	4
21	M 10	34	44	57	74	10	4,3	8,4	5
21	M 12	34	57	74	94	10	3,4	10,8	6
25	M 8	20	35	45	58	10,5	5,5	6,8	4
25	M 10	34	44	57	74	10,5	4,6	8,4	5
25	M 12	34	57	74	94	10,5	3,6	10,8	6
32	M 8	20	35	45	58	11	6	6,8	4
32	M 10	34	44	57	74	11	5	8,4	5
32	M 12	34	57	74	94	11	4,2	10,8	6
40	M 8	20	35	45	58	13	8	6,8	4
40	M 10	34	44	57	74	13	7	8,4	5
40	M 12	34	57	74	94	13	6,2	10,8	6

Specification

- Screw
 - Steel **ST**
Property class 5.8
Blackened
 - Stainless steel AISI 303 **NI**
- Hex nuts ISO 4032
 - Steel
 - Zinc plated, blue passivated
 - Stainless steel AISI 303
- Thrust pad
 - Plastic (Polyacetal POM)
 - Temperature resistant up to 80 °C
 - Black, matte finish
- Stainless Steel Characteristics → Page 2166
- RoHS

4

Information

The ball end of the grub screw can be hit easily into the thrust pad and removed.

The two hex nuts are included parts of the order.

see also...

- Holders for Clamping Screws GN 801 (for Toggle Clamps with Forked Clamping Arm) → Page 815

How to order (Steel)

1 2 3 4
GN 903-18-M8-35-ST

1	d ₁
2	d ₂
3	l ₁
4	Material

How to order (Stainless steel)

1 2 3 4
GN 903-21-M12-57-NI

1	d ₁
2	d ₂
3	l ₁
4	Material