



b	d₁ F9				d₂	l₁	l₂	l₃	l₄	l₅	m₁	m₂	m₃	m₄
33	B 8	B 10	B 12	B 14	4,5	47	30,5	9,5	24,5	22	20	21	23,5	20

Specification

Clamping plate

Zinc die casting
Powder coated
Black, textured finish

Adjustable clamping lever GN 302.1

- Handle
Zinc die casting
Powder coated
Black, RAL 9005, textured finish
- Insert / Retaining screw
Stainless steel AISI 303

RoHS

Clamping plates GN 954.7 are used in connection with position indicators GN 954 / GN 954.2. The mounting holes support typical bore hole patterns. In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the hand lever is situated as required either on the right or the left.

see also...	Page
GN 954 Position Indicators (Hollow Shaft Steel)	QVX
GN 954.2 Position Indicators (Hollow Shaft Stainless Steel)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN954.7-33-B10

1	b
2	d ₁

