



b	d <sub>1</sub> F9					d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	m <sub>4</sub>	m <sub>5</sub>
48	B 12	B 14	B 15	B 16	B 20	5,5	73	40,5	18	24,5	30	34	36	33,6	25	17

**Specification**

**Clamping plate**

- Zinc die casting
- Powder coated
- Black, textured finish

**Adjustable hand lever GN 302.1**

- Handle
  - Zinc die casting
  - Powder coated
  - Black, RAL 9005, textured finish
- Insert / Retaining screw
  - Stainless steel AISI 303

RoHS

Clamping plates GN 9053.6 are used in connection with position indicators GN 9053 and GN 9153. The mounting holes support typical hole patterns.

In a simpler way and without large construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with the bore Ø 6,1 to accept the torque limiter for the position indicator.

The clamping plate can be installed so that the hand lever is positioned either to the right or the left.

see also...	Page
GN 9053 Position Indicators (Electronic)	QVX
GN 9153 Position Indicators (Electronic, Data Transmission via Radio Frequency)	QVX

**Technical Information**

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN 9053.6-48-B12

1	b
2	d <sub>1</sub>

