



- 3 Type**
- A** without micro encapsulation
 - GPC** with micro encapsulation

2

2

d		d		h	s
Steel ST	Stainless Steel NI	Steel ST	Stainless Steel NI		
M 6 x 1	-	-	-	6	3
M 8 x 1	M 8 x 1	-	-	8	4
M 10 x 1	M 10 x 1	R 1/8	R 1/8	8	5
M 12 x 1,5	M 12 x 1,5	-	-	10	6
M 14 x 1,5	M 14 x 1,5	R 1/4	R 1/4	10	7
M 16 x 1,5	M 16 x 1,5	-	-	10	8
M 18 x 1,5	M 18 x 1,5	R 3/8	R 3/8	10	8
M 20 x 1,5	M 20 x 1,5	R 1/2	R 1/2	10	10
M 22 x 1,5	M 22 x 1,5	-	-	10	10
M 24 x 1,5	M 24 x 1,5	-	-	12	12
M 26 x 1,5	-	R 3/4	R 3/4	12	12
M 30 x 1,5	-	R 1	R 1	12	17
M 36 x 1,5	-	-	-	15	19
M 42 x 1,5	-	R 1 1/4	-	18	22
M 45 x 1,5	-	-	-	18	22
M 48 x 1,5	-	R 1 1/2	-	20	24

Specification

- Steel **ST**
 - ultrasonically and tensile tested
 - zinc plated, blue passivated
- Stainless Steel AISI 303 **NI**
- Thread coating **GPC** (Precote 5) → Page 1497
- *Stainless Steel characteristics* → Page 1489
- RoHS

1

Information

Threaded plugs DIN 906 are used to close bore holes with cylindrical internal thread.

The tightness depends on the medium, pressure, temperature and material pairing. The design with GPC thread coating provides a higher degree of safety.

How to order

DIN 906-ST-M36x1,5-GPC

- 1 Material**
- 2 d**
- 3 Type**