


- 5 Type**
- A** Without assembly set, without cover cap
 - B** With assembly set, with cover cap
 - C** With assembly set, without cover cap



1		2	3	4							
b_1	n	l_1	l_2	b_2	h	l_3	l_4	l_5	l_6	s	
Nominal dimension	Actual dimension										
30	28	8	30	30	6,3	2,1	3	9,7	10,4	6,8	5,9
40	38	10	40	40	8,5	4,1	4	9,5	20	7,2	5,6
45	43	10	45	45	8,5	4,1	4	15,7	18,7	11,5	9,7

Specification

- Aluminum die casting
 - Matte, tumbled **MT**
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Silver, RAL 9006, textured finish **● SR**
- T-slot bolt GN 505.4 with hexagon flange nut DIN 6923
Steel
Zinc plated, blue passivated
- T-nut GN 505 with socket head cap screw DIN 7984
Steel
Zinc plated, blue passivated
- Cover cap
Plastic (Polyamide PA)
Black, matte finish
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

To mount angle pieces GN 960 in place, insert the assembly sets into the profile slot through the opening. When tightening, the nut or bolt will be cross-positioned and thus anchored in the slot.

For crossing profiles or when using the angle pieces with components without a slot, the removable guide steps can simply be snapped off.

After assembly, the cover caps are snapped into place via four lugs. They give the angle piece an attractive appearance and protect against dirt.

Even after repeated use, the cover caps will remain firmly attached to the angle pieces, thanks to the elastic snap-type lugs. If required, they are also available individually under standard GN 963 → Page 1826.

see also...

- *T-Slot Bolts GN 505.4* → Page 1168
- *T-Nuts GN 505* → Page 1169

How to order

1	b_1
2	n
3	l_1
4	l_2
5	Type
6	Finish

GN960-45-10-45-45-A-SW

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9