



3 Type

- A** Semi-spherical pivot
- B** Pointed pivot

1

2

d ₁	l ₁ Nominal length					d ₂	l ₂	l ₃	r	A/F
M 5	8	12	16	20	-	3	1	0,5	2,5	2,5
M 6	12	16	20	25	-	4	1,8	0,8	3	3
M 8	12	16	20	25	32	6	2,5	1	5	4
M 10	16	20	25	32	40	8	3,5	1,5	6	5

Specification

- Steel
 - Property class 5.8
 - Blackened
- Thrust pivot
Hardened
- *Strength Values of Screws* → Page 2152
- RoHS

Information

Grub screws GN 913.2 with hardened spherical pivot (Type A) are used in such cases where point contact is required. They are a lower cost alternative to ball point screws GN 605.

Grub screws with hardened pointed pivot (Type B) offer an alternative form of finish.

see also...

- *Ball Point Screws GN 605 (with Full Ball)* → Page 1052
- *Grub Screws GN 913.3 (with Brass / Plastic Pivot)* → Page 1048
- *Grub Screws GN 913.6 (with Retaining Magnet)* → Page 2067

How to order

GN913.2-M6-20-B

- 1** d₁
- 2** l₁
- 3** Type