



d ₁	1 2										d ₂	d ₃	l ₂	l ₃ ±0,3	A/F ₁	A/F ₂
	Nominal length															
M 3	3	4	5	6	8	10	-	-	-	-	1,9	1,5	0,5	0,8	1,5	1,5
M 4	4*	5*	6	8	10	12	16	20	-	-	2,5	2	0,5	1	2	1,5
M 5	5*	6*	8	10	12	16	20	25	-	-	3	3	0,5	1	2,5	2,5
M 6	6	8	10	12	16	20	25	32	40	50	4	3,5	1	1,3	3	3
M 8	8	10*	12	16	20	25	32	40	50	63	6	5	1,5	1,6	4	4
M 10	16	20	25	32	40	50	63	80	-	-	8	6,5	2	1,9	5	5
M 12	20	25	32	40	50	63	80	100	-	-	10	8	2	2,1	6	6

* These lengths are only available with brass pivot.

Specification

- Screw Steel
 - Tensile strength class 5.8
 - blackened

• Thrust pivot

- Brass **MS**
- Plastic (Polyacetal POM) **KU**

• Strength values of screws → Page 1481

• Plastic characteristics → Page 1483

• RoHS

3

Information

Grub screws GN 913.3 with pivots in brass or plastic are used in applications, where marks and damage on the workpiece are unacceptable.

see also...

- Grub screws GN 913.2 (with hardened thrust pivot) → Page 780
- Ball point screws GN 605 (with flat ball) → Page 782

How to order

GN 913.3-M6-20-MS

1	d ₁
2	l ₁
3	Thrust pivot