







Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 127 → Page XYZ					
	GN 127-...-B	-		GN 968-10-M6-20-B ¹⁾	
Mounting plate GN 139.3 (for hinges with / without safety switch GN 139.1 / GN 139.2) → Page XYZ					
	GN 139.3-170	GN 968-8-M6-10-A		GN 968-10-M6-14-A	
Mounting plate GN 139.4 (for hinges with / without safety switch GN 139.1 / GN 139.2) → Page XYZ					
	GN 139.4-101	GN 968-8-M6-10-A		GN 968-10-M6-14-A	
Flanged connector clamps GN 145 → Page XYZ					
	GN 145-...	-		GN 968-10-M5-18-A	
Hinges GN 151.4 → Page XYZ					
	GN 151.4-...-B	-		GN 968-10-M6-18-A ¹⁾	
Hinges GN 159 → Page XYZ					
	GN 159-54-17,5-17,5 GN 159-74-22,5-22,5 GN 159-84-25-25	GN 968-8-M6-16-B - -		- GN 968-10-M6-18-B ¹⁾ GN 968-10-M6-18-B ²⁾	
Double hinges GN 159.1 → Page XYZ					
	GN 159.1-89-35-35 GN 159.1-119-45-45 GN 159.1-134-50-50	GN 968-8-M6-16-B - -		- GN 968-10-M6-18-B ¹⁾ GN 968-10-M6-18-B ²⁾	



¹⁾ only for profile 40 x 40 ²⁾ only for profile 45 x 45

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges GN 161 → Page XYZ					
	GN 161-57 / 68 / 80	GN 968-8-M6-14-B		GN 968-10-M6-18-B	
Base plate connector clamps GN 162.3 → Page XYZ					
	GN 162.3-...	GN 968-8-M5-14-A		GN 968-10-M5-18-A	
Foot clamp mountings GN 175 → Page XYZ					
	GN 175-B10 GN 175-B12 GN 175-B14	GN 968-8-M6-10-A		GN 968-10-M6-14-A	
Fastening sets GN 181 (for cabinet „U“ handles) → Page XYZ					
	GN 181-ZD-10-M5-... GN 181-ZD-... -M6-... GN 181-ZD-... -M8-...	GN 968-8-M5-12-B GN 968-8-M6-12-B -		- GN 968-10-M6-16-B GN 968-10-M8-16-B	
Tube supports GN 231 → Page XYZ					
	GN 231-B20 / B25 / B30 GN 231-V20 / V25 / V30	- -		GN 968-10-M8-14-A GN 968-10-M8-14-A	
Hinge GN 236 → Page XYZ					
	GN 236-75-60	-		GN 968-10-M6-20-B ¹⁾	
Hinge GN 239.3 → Page XYZ					
	GN 239.3-70-60-SH	-		GN 968-10-M6-18-B ¹⁾	



¹⁾ only for profile 40 x 40



Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Hinges with safety switch GN 239.4 → Page XYZ					
	GN 239.4-...	-		GN 968-10-M6-18-B ¹⁾	
Hinges with safety switch GN 239.6 → Page XYZ					
	GN 239.6-60-110-...	-		GN 968-10-M6-18-B ¹⁾	
Hinges GN 239.7 → Page XYZ					
	GN 239.7-60-70 GN 239.7-60-110	-		GN 968-10-M6-18-B ¹⁾	
Mounting plates GN 239.8 (for hinges GN 239.6 / GN 239.7) → Page XYZ					
	GN 239.8-110-14-... GN 239.8-110-19-... GN 239.8-110-21-...	GN 968-8-M6-14-B - -		- GN 968-10-M6-18-B GN 968-10-M6-18-B	
Swivel clamp connector bases GN 271 → Page XYZ					
	GN 271-25-...	-		GN 968-10-M5-18-A	
Sensor holders GN 271.4 → Page XYZ					
	GN 271.4-B12-... GN 271.4-B18-...	- -		GN 968-10-M5-18-A	
Swivel clamp connector joints GN 281 → Page XYZ					
	GN 281-...	-		GN 968-10-M5-18-A	

¹⁾ only for profile 40 x 40



Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Tubular handles GN 333 → Page XYZ					
	GN 333-28-...-B-...	GN 968-8-M6-25-A		GN 968-10-M6-28-A	
Tubular handles GN 333.1 → Page XYZ					
	GN 333.1-28-...-B-...	GN 968-8-M6-14-C		GN 968-10-M6-18-C	
Oval tubular handles GN 334.1 → Page XYZ					
	GN 334.1-36-...	-		GN 968-10-M8-16-C	
Indexing plungers GN 412 → Page XYZ					
	GN 412-8-47-...-1 GN 412-10-47-...-1	GN 968-6-M5-18-A GN 968-6-M5-18-A		GN 968-8-M5-20-A GN 968-8-M5-20-A	
Mounting blocks GN 412.1 → Page XYZ					
	GN 412.1-47-...-1	GN 968-8-M5-18-A		-	
Spring latches GN 416 → Page XYZ					
	GN 416-6-38 GN 416-8-38 GN 416-8-46 GN 416-10-38 GN 416-10-46 GN 416-12-46	GN 968-8-M5-14-A GN 968-8-M5-14-A - GN 968-8-M5-14-A - -		GN 968-10-M5-18-A GN 968-10-M5-18-A GN 968-10-M6-18-A GN 968-10-M5-18-A GN 968-10-M6-18-A GN 968-10-M6-18-A	





Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Locators GN 416.1 → Page XYZ					
	GN 416.1-6-38 GN 416.1-8-38 GN 416.1-8-46 GN 416.1-10-38 GN 416.1-10-46 GN 416.1-12-46	GN 968-8-M5-14-A GN 968-8-M5-14-A - GN 968-8-M5-14-A - -	GN 968-10-M5-18-A GN 968-10-M5-18-A GN 968-10-M6-18-A GN 968-10-M5-18-A GN 968-10-M6-18-A GN 968-10-M6-18-A		
Indexing plungers GN 417 → Page XYZ					
	GN 417-5-A / -B / -C GN 417-6-A / -B / -C GN 417-8-A / -B GN 417-8-C GN 417-10-A / -B / -C	GN 968-8-M4-12-A GN 968-8-M5-14-A GN 968-8-M5-14-A - -	- GN 968-10-M5-18-A GN 968-10-M6-18-A GN 968-10-M5-18-A GN 968-10-M6-18-A		
Locators GN 417.1 → Page XYZ					
	GN 417.1-5 GN 417.1-6 GN 417.1-8 GN 417.1-10	GN 968-8-M4-12-A GN 968-8-M5-14-A GN 968-8-M5-14-A -	- GN 968-10-M5-18-A GN 968-10-M5-18-A GN 968-10-M6-18-A		
Stainless Steel-Locators GN 417.1 → Page XYZ					
	GN 417.1-5-NI-GS GN 417.1-6-NI-GS GN 417.1-8-NI-GS GN 417.1-10-NI-GS	GN 965-6-M4-12-A GN 965-6-M5-14-A GN 965-6-M5-14-A -	- GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A		
Base clamp mountings GN 473 → Page XYZ					
	GN 473-B8-... GN 473-B10 / B12-... GN 473-B15 / B16-... GN 473-B20-...	GN 968-8-M4-10-A - - -	GN 968-10-M4-14-A GN 968-10-M5-14-A GN 968-10-M6-14-A GN 968-10-M6-18-A		
Clamp mountings GN 477 → Page XYZ					
	GN 477-B8-... GN 477-B10 / B12-... GN 477-B15 / B16 / B20-...	GN 968-8-M4-16-A GN 968-8-M5-18-A GN 968-8-M6-20-A	- GN 968-10-M5-20-A GN 968-10-M6-22-A		

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Flange bolts GN 480 → Page XYZ					
	GN 480-8-... GN 480-10 / 12-... GN 480-15 / 16 / 20-...	GN 968-8-M4-10-A GN 968-8-M5-10-A GN 968-8-M6-12-A	- GN 968-10-M5-12-A GN 968-10-M6-14-A		
Cabinet U-Handles GN 528 → Page XYZ					
	GN 528-...-94-6,5-... GN 528-...-117-6,5-... GN 528-...-117-8,5-... GN 528-...-122-8,5-... GN 528-...-132-8,5-... GN 528-...-140-8,5-... GN 528-...-160-8,5-... GN 528-...-179-8,5-... GN 528-...-235-8,5-...	GN 968-8-M6-14-A GN 968-8-M6-16-A - - - - - - -	GN 968-10-M6-16-A GN 968-10-M6-20-A GN 968-10-M8-16-A GN 968-10-M8-16-A GN 968-10-M8-18-A GN 968-10-M8-18-A GN 968-10-M8-20-A GN 968-10-M8-20-A GN 968-10-M8-20-A		
Angle connector brackets GN 561 → Page XYZ					
	GN 561-19-...-A / -B / -C GN 561-25-...-A / -B / -C GN 561-43-...-A	GN 968-8-M6-14-C GN 968-8-M6-14-C -	- - GN 968-10-M8-18-C		
Cabinet U-Handles GN 565.1 → Page XYZ					
	GN 565.1-20-... GN 565.1-26-...	GN 968-8-M5-20-A -	- GN 968-10-M6-22-A		
Inclined cabinet U-Handles GN 565.2 → Page XYZ					
	GN 565.2-26-128-B-... GN 565.2-26-160-B-...	- -	GN 968-10-M6-22-C GN 968-10-M6-22-C		
Cam action indexing plungers GN 612.2 → Page XYZ					
	GN 612.2-...-16-... GN 612.2-...-20-...	GN 968-8-M5-18-A GN 968-8-M5-22-A	- GN 968-10-M5-25-A		



Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Cam action indexing plungers GN 612.9 → Page XYZ					
	GN 612.9-...-16-... GN 612.9-...-20-...	GN 968-8-M5-18-A GN 968-8-M5-22-A	- GN 968-10-M5-25-A		
Cabinet U-Handles GN 628 → Page XYZ					
	GN 628-...-117-6,5-B-... GN 628-...-117-8,5-B-... GN 628-...-150-8,5-B-... GN 628-...-179-8,5-B-...	GN 968-8-M6-14-A - - -	- GN 968-10-M8-28-A GN 968-10-M8-28-A GN 968-10-M8-28-A		
Ledge handles GN 630 → Page XYZ					
	GN 630-114-B-...	GN 968-8-M6-18-B	GN 968-10-M6-22-B		
Cabinet U-Handles GN 630.1 → Page XYZ					
	GN 630.1-114-B-...	GN 968-8-M6-18-B	GN 968-10-M6-22-B		
Panel support clamp GN 649 → Page XYZ					
	GN 649-35-E	GN 968-8-M6-10-D	GN 968-10-M6-14-D		
Cabinet U-Handles GN 667 → Page XYZ					
	GN 667-20-...	-	GN 968-10-M8-20-A		
Cam action indexing plungers GN 722.3 → Page XYZ					
	GN 722.3-8-... GN 722.3-10-... GN 722.3-12-... GN 722.3-14-...	- - - -	GN 968-10-M6-18-A GN 968-10-M6-18-A GN 968-10-M6-18-A GN 968-10-M6-18-A		

Assembly sets GN 968		Type A	Type B	Type C	Type D
					
Compatible GN standards in ascending order of the standard numbers					
Cabinet U-Handles GN 728 → Page XYZ					
	GN 728-120-B-... GN 728-180-B-...	GN 968-8-M6-14-A -	GN 968-10-M8-18-A		
Cabinet U-Handles GN 728.5 → Page 92					
	GN 728.5-120-B-...	GN 965-6-M6-14-A	-		
Slam latches GN 936 → Page XYZ					
	GN 936-72-...	GN 968-8-M6-12-A	GN 968-10-M6-14-A		
Angle pieces / Shackles GN 967 → Page XYZ					
	GN 967-...-20-...-1-...	GN 968-8-M5-12-A	GN 968-10-M5-14-A		
	GN 967-...-20-...-2-...	GN 968-8-M5-12-B	GN 968-10-M5-14-B		
	GN 967-...-30-...-1-...	GN 968-8-M6-12-A	GN 968-10-M6-14-A		
	GN 967-...-30-...-2-...	GN 968-8-M6-12-B	GN 968-10-M6-14-B		
	GN 967-...-40-...-1-...	-	GN 968-10-M8-16-A		
	GN 967-...-40-...-2-...	-	GN 968-10-M8-16-B		
	GN 967-...-45-...-1-...	-	GN 968-10-M8-16-A		
	GN 967-...-45-...-2-...	-	GN 968-10-M8-16-B		
Threaded flanges GN 3490 → Page XYZ					
	GN 3490-45-... GN 3490-60-...	GN 968-6-M6-14-B -	GN 968-8-M8-16-B GN 968-8-M8-16-B		
Ball-shaped door locks GN 4490 → Page XYZ					
	GN 4490-ZD-50... GN 4490-ZD-68... GN 4490-ZD-80...	GN 968-6-M4-10-B GN 968-6-M4-10-B GN 968-6-M5-14-B	GN 968-8-M4-12-B GN 968-8-M4-12-B GN 968-8-M5-14-B		

