



**2 Bore code**

- B** without keyway
- K** with keyway

**4 Type**

- A** without handle
- R** with revolving handle

**1** **3**

d <sub>1</sub>	d <sub>2</sub> H7 Bore	d <sub>3</sub>	d <sub>4</sub>	b	h	l <sub>1</sub>	l <sub>2</sub> ≈	l <sub>3</sub> ≈	r	Ø Handle GN 798.2	recommended countersunk washer	
125	12	14	31	23	15	11	18	33,5	61,5	45,5	22	GN 184-20
140	14	16	36	28,5	16,5	13	19	36,5	76,5	52	24	GN 184-25
160	14	16	36	28,5	18	14,5	20	39,5	76,5	61	24	GN 184-25
200	18	20	42	36	20,5	16	24	45,5	85	77,5	25	GN 184-32

**Specification**

- Aluminum die casting
  - Hub machined
  - Rim turned
  - plastic coated
    - black, RAL 9005, textured finish ● **SW**
    - silver, RAL 9006, textured finish ● **SR**
- Rim concentric and square to bore < 0,4
- Revolving handles GN 798.2
  - Plastic, Technopolymer  
black, matte
  - Spindle steel  
zinc plated, blue passivated
- *Keyway P9 DIN 6885 Page 1 → Page 1420*
- *Cross holes GN 110 → Page 1422*
- *ISO-Fundamental tolerances → Page 1479*
- **RoHS**

**Accessory**

- Countersunk washers GN 184 → Page 814

**5**

**Information**

Spoked handwheels GN 924 are distinguished by modern design. The removable plastic cover shrouds the fixing components such as screws, countersunk washers as well as the shaft end.

see also...

- *Spoked handwheels GN 322 (Aluminum, rim polished) → Page 176*

**How to order**

<b>1</b>	d <sub>1</sub>
<b>2</b>	Bore code
<b>3</b>	d <sub>2</sub>
<b>4</b>	Type
<b>5</b>	Color

**GN 924-125-K12-A-SR**