



d Ø	w	l <sub>1</sub>	l <sub>2</sub>	for tube
D 10	1 ... 2	3,5	11	GN 990
D 12	1 ... 2	3,5	11	GN 990
D 13	1 ... 2	4	11	¼"
D 14	1 ... 2	5	11,5	GN 990
D 15	1 ... 2	3	11,5	GN 990
D 16	1 ... 2	5	11	GN 990
D 18	1 ... 2	5	11,5	GN 990
D 20	1 ... 2,5	5	11,5	GN 990
D 22	1 ... 2	5	11,5	-
D 25	1 ... 3	5	11,5	GN 990
D 26	1 ... 3	5	11,5	-
D 27	1 ... 3	5	11,5	¾"
D 28	1 ... 3	5	11,5	-
D 30	1 ... 2,5	5	11,5	GN 990
D 32	1 ... 3	5	12	GN 990
D 34	1 ... 3	5	11,5	1"

d Ø	w	l <sub>1</sub>	l <sub>2</sub>	for tube
D 35	1 ... 3	5	11,5	GN 990
D 36	1 ... 3	5	11,5	-
D 38	1 ... 3,5	5	11,5	-
D 40	1 ... 3	5	11,5	GN 990
D 42	1 ... 3	5	11,5	GN 990
D 45	1 ... 3	5	11	GN 990
D 48	1,2 ... 3,6	5	11,5	GN 990
D 50	2,5 ... 4,5	5	11,5	GN 990
D 55	3 ... 5	5	14,5	GN 990
D 60	3 ... 5	5	17,5	GN 990
D 70	1,5 ... 3,5	5	21	-
D 76	1,6 ... 4	6	21,5	2 ½"
D 80	1,5 ... 3	5	22	-
D 88	1,5 ... 4	6	21,5	3"
D 90	1,5 ... 5	6	21	-
D 100	2 ... 4,5	6	28,5	-

s ∇	w	l <sub>1</sub>	l <sub>2</sub>	for tube
V 10	0,8 ... 2,5	4	12	GN 990
V 12	1 ... 2	4	12	GN 990
V 15	1 ... 2	3	11,5	-
V 16	1 ... 2,5	5	11,5	GN 990
V 18	1,5 ... 3	5	11,5	-
V 20	1 ... 3	5	11,5	GN 990
V 22	1 ... 3,5	5	12	-
V 25	1 ... 3	5	11,5	GN 990
V 30	1 ... 3	5	11,5	GN 990
V 34	1 ... 3	5	14,5	-
V 35	1 ... 3	5	11,5	GN 990
V 40	1 ... 3	5	14,5	GN 990
V 45	1 ... 3	5	14,5	GN 990
V 50	2,6 ... 4	5,5	24	GN 990
V 55	2 ... 4,5	5	14,5	-
V 60	1,5 ... 3,5	5	15	-
V 70	2 ... 5	5	22	-
V 80	1,5 ... 4	6	21	-
V 90	3 ... 5	6	21	-
V 100	1 ... 4	7	21	-

**Specification**

- Plastic Technopolymer (Polyethylen PE)
  - black, RAL 9005, matt  SW
  - grey, RAL 7042, matt  GR
- Plastic characteristics → Page 1489
- RoHS compliant

**On request**

- other sizes
- white, RAL 9003, matte  WS



**Information**

Tube end plugs GN 991 have been designed for sealing tube ends for safety or optical reasons.

They are pressed into the tube end either by hand or with a mallet.

see also...

- Construction tubes GN 990 → Page 1277
- Retaining rods / Retaining tubes GN 480.1 → Page 1276
- Insert bushings GN 992 (Aluminum, with female thread) → Page 1059

How to order	1 s (d)
<b>GN991-V25-GR</b>	2 Color