



1

2

d ₁ ±0,2	Length l ±0,25						d ₂	for thread tapping screws DIN 7500
20	194	244	294	394	-	-	4,5	M 5
28	192	242	292	392	492	592	5,5	M 6
30	189	289	389	489	589	989	3,6	M 4

Specification

3

- Aluminum
 - plastic coated black, RAL 9005, textured finish (available up to 3000 mm length)
 - anodized, natural color (available up to 2600 mm length)

● SW

● EL

• RoHS

On request

- Plastic cover in black or light gray for tube Ø 28

Information

Handle tubes GN 930 with screw channel are designed for use in a variety of different tube handles (e.g. GN 333).

For applications not requiring handle bases, the screw channel provides a very economical fixing solution with thread-tapping screws. The lengths l listed in the table are ex stock lengths. Depending to the finish, any lengths until max. 3000 mm are available.

see also...

- Handle shanks GN 333.8 (for tubular handles Ø 28, angled) → Page 135
- Handle shanks GN 333.9 (for tubular handles Ø 28, straight) → Page 135

How to order

GN 930-30-989-EL

1	d ₁
2	Length l
3	Finish

