


Rost frei®
Inox
Stainless
Steel

- 3 Type**
- MS** Brass pivot
 - KU** Plastic pivot (Polyacetal POM)
 - ZK** Spherical pivot



d ₁	l ₁ Nominal length						d ₂	d ₃	d ₄ +0,05	l ₂	l ₃	l ₄	l ₅ ≈	A/F
	6	8	10	12	15	20								
M 6	16*	20	25	30	35	4	3,5	4,5	1	1,3	4	5,1	10	
M 8	20*	25	30	35	45	6	5	6,1	1,5	1,6	5,3	6,2	13	
M 10	25*	30	35	45	55	8	6,5	7,8	2	1,9	6,4	7,3	17	

*only available in type MS and KU

Specification

- Stainless steel AISI 304
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Stainless steel hex head screws GN 933.5 with brass or plastic pivots are used when pressure dents or damage to the clamping surface must be avoided.

The type with sperical pivot has a ball diameter d₄ which is smaller than the core diameter d₁ of the thread. This makes them suitable for holding thrust pads GN 631 /GN 631.5 which must be ordered separately.

see also...

- *Stainless Steel Grub Screws GN 913.5* → Page 1049
- *Thrust Pads GN 631 (Plastic)* → Page 1071
- *Stainless Steel Thrust Pads GN 631.5* → Page 1071

How to order GN933.5-M6-20-KU	1	d ₁
	2	l ₁
	3	Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9