



**2 Installation (Front view)**

- AN** On the chamfer, above
- AR** On the chamfer, below
- FN** In the front, above
- FR** In the front, below

**3 Type**

- R** Numbers ascending clockwise
- L** Numbers ascending anti-clockwise



**1**

Counter	Indication after one spindle revolution	Corresponds to thread pitch	Max. revolutions per minute
00.50	0050	0,5	500
01.00	0100	1	250
001.0	0010	1	1500
001.25	00125	1,25	1500
001.5	0015	1,5	1500
002.0	0020	2	1250
002.5	0025	2,5	1000
003.0 *	0030	3	830
004.0 **	0040	4	625
005.0	0050	5	500
006.0	0060	6	415
008.0	0080	8	315
010.0	0100	10	250

\* Suitable for linearer actuators GN 291 ff. Ø 18    \*\* Suitable for linearer actuators GN 291 ff. Ø 30

**Specification**

- Housing  
Plastic (Polyamide PA)  
- Orange, RAL 2004 ● **OR**  
- Gray, RAL 7035 ● **GR**  
- Black-gray RAL 7021 ● **SG**
- Temperature resistant up to 80 °C
- Oil and solvent proof
- Numbers white, number wheels for integers black, decimals red with additional scale
- Hollow shaft stainless steel AISI 303
- *Stainless Steel Characteristics* → Page QVX
- **RoHS**

**On request**

- Other counter display

**4**

**Information**

Position indicators GN 954.2 are fitted with a direct drive counter with digital read out. Both housing sections are ultrasonically welded, making the housing very tightly seated, stable and compact.

The foam rubber seal prevents the transmission of vibration to the counter and also acts as a seal.

see also...

- *More Information to Position Indicators* → Page 394
- *Adapter Bushings GN 952.1 (for Position Indicators)* → Page 412
- *Control Knobs GN 957 (for Position Indicators)* → Page 413
- *Clamping Plates GN 954.6 (for Position Indicators)* → Page 414

<p><b>How to order</b></p> <p><b>GN954.2-001.0-FR-R-GR</b></p>	1	Counter
	2	Installation (Front view)
	3	Type
	4	Color

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4