



**4 Type**  
**M** Straight lever  
**N** Angled lever

**1** **2** **3**

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub> ≈	l <sub>2</sub>	l <sub>3</sub> ≈
10	M 8	20	13,5	20	25	8	39,5	63	60
13	M 10	20	16	25	29	8	49,5	80	76
16	M 12	25	19	28	33,5	10,5	60,5	100	95

**Specification**

- Steel blackened  
 Threaded stud  
 Tensile strength class 5.8
- *Strength values of screws → Page 1481*
- RoHS

**Information**

Adjustable clamping levers GN 99.2 are known for their small dimensions. They are for use in applications where either the clamping range is limited or where a specific lever position is required. The serrated bore in the spherical hub is fitted with a threaded bolt insert which engages in the hub with its own serrations.

By depressing the clamping lever the serrations are disengaged freeing it for re-positioning in the most convenient position. When releasing the lever the serrations will re-engage automatically.

Should a rotation of 360° not be possible the insert can be slightly screwed in (after the lever has been disengaged) by means of the slotted knurled screw.

**How to order**

**GN 99.2-13-M10-40-N**

- 1** d<sub>1</sub>
- 2** d<sub>2</sub>
- 3** l<sub>1</sub>
- 4** Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

