

Telescopic Slides

Overview of Types



Standard	Type of extension	Load capacity Per pair at 10,000 cycles in N	Basic length Retracted position in mm	Material Steel ST SST NI	Mounting		
	Partial extension T Full extension V				Through-holes (ld. no. 1)	Countersunk holes (ld. no. 2)	Outer slide, through-holes / Inner slide, countersunk holes (ld. no. 3)
GN 1400 Page 1854	T	280	300 - 500	ST	×		
GN 1404 Page 1856	T	780	300 - 700	ST			×
GN 1408 Page 1858	V	250	250 - 700	ST	×		
GN 1410 Page 1861	V	510	250 - 800	ST	×		
GN 1412 Page 1864	V	430	300 - 700	ST	×		
GN 1414 Page 1867	V	360	300 - 650	ST	×		
GN 1418 Page 1870	V	430	350 - 650	ST	×		
GN 1420 Page 1873	V	1290	300 - 1200	ST		×	
GN 1422 Page 1875	V	1290	300 - 800	ST		×	
GN 1424 Page 1878	V	750	350 - 700	ST		×	
GN 1426 Page 1881	V	1380	500 - 800	ST		×	
GN 1430 Page 1883	V	2120	400 - 1200	ST		×	
GN 1432 Page 1885	V	2300	400 - 800	ST		×	
GN 1440 Type B Page 1888	V	3250	300 - 1500	ST	×		
GN 1440 Type M Page 1888	V	3250	300 - 1500	ST	×		
GN 1440 Type K Page 1888	V	3250	300 - 1500	ST	×		
GN 1440 Type Q Page 1888	V	3250	300 - 1500	ST	×		
GN 1450 Page 1891	V	510	300 - 600	NI	×		
GN 1460 Page 1894	V	1050	250 - 800	NI		×	

Standard	Component features									
	Without rubber stop	With rubber stop back-front	Locking device back Type E	Locking device back, detach function Type F	Latch back Type M	Latch front Type K	Latch back-front Type Q	Self-retracting mechanism, dampened / not dampened	Push to open mechanism	Extension on both sides
GN 1400 Page 1854	×									
GN 1404 Page 1856		×	×							
GN 1408 Page 1858		×		×						
GN 1410 Page 1861		×		×						
GN 1412 Page 1864		×		×				×		
GN 1414 Page 1867		×		×				×		
GN 1418 Page 1870		×		×					×	
GN 1420 Page 1873		×	×							
GN 1422 Page 1875		×						×		
GN 1424 Page 1878		×						×		
GN 1426 Page 1881		×								×
GN 1430 Page 1883		×	×							
GN 1432 Page 1885		×						×		
GN 1440 Type B Page 1888		×								
GN 1440 Type M Page 1888		×			×					
GN 1440 Type K Page 1888		×				×				
GN 1440 Type Q Page 1888		×					×			
GN 1450 Page 1891		×		×						
GN 1460 Page 1894		×		×						

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

