



3 Type

F With fixed handle

No.	d ₁ H7 Bore	d ₂	d ₃	d ₄	d ₅	h ₁	h ₂ ≈	Length l
100	B 7	13	16	18	10	13	31	25
101	B 8	15	19	20	13	17	40	28
102	B 8	16	20	22	14	17	45	34
103	B 10	18	23	25	16	19,5	50	41
104	B 12	20	26	28	18	21,5	56	50

Specification

- Steel
 - Turned
 - Zinc plated, blue passivated
- Fixed handles DIN 39
 - Steel zinc plated, blue passivated
- *ISO Fundamental Tolerances* → Page 2151
- RoHS

Information

Tri-ball handles GN 10 allow fine adjustment.

An alternative in modern design are cranked handles GN 510 and control handles GN 112.1.

see also...

- *Cranked Handles GN 510 (Plastic)* → Page 297

How to order

GN 10-104-B12-F

1	No.
2	d ₁
3	Type