



**GN 650**  
Page 1564



**Features:**

- $l_1$ : 76 / 127 / 254
- With and without thermometer


**GN 650.1**  
Page 1564



**Features:**

- Identical in construction to GN 650, but
- Mountings elements made of stainless steel
  - Seals made of FPM rubber (Viton®)


**GN 650.2**  
Page 1566



**Features:**

- $l_1$ : 127 (Version P)
- $l_1$ : 76 / 127 / 254 (Version PT)
- With and without thermometer
- With protective housing (bumpers) in zinc die casting (P) or in Kunststoff (PT)


**GN 650.4**  
Page 1567



**Features:**

- $l_1$ : 76 / 127
- With and without thermometer
- With and without protective housing (bumpers)
- Narrow, economical version
- Mounting elements made of stainless steel or plastic


**GN 656**  
Page XYZ



**Features:**

- $l_1$ : 127
- With electrical oil level monitoring
- with axial plug


**GN 656.1**  
Page XYZ



**Features:**

- $l_1$ : 76 / 127 / 254
- With electrical oil level monitoring
- with lateral plug


**GN 654**  
Page 1576



**Features:**

- $l_1$ : 127 / 176 / 254 / 381 / 508
- With crystal clear plastic indicator tube made from Polycarbonate PC


**GN 654.1**  
Page 1576



**Features:**

- $l_1$ : 76 / 127 / 176 / 254 / 381 / 508
- Identical in construction to GN 654 but higher chemical resistance due to
- Plastic indicator tube made from borosilicate glass (Pyrex®)
- Mounting elements made of stainless steel
- Seals made of FKM rubber (Viton®)


**GN 654.2**  
Page 1578



**Features:**

- Assembly sets for GN 654 / GN 654.1
- For electrical fluid level monitoring
- With 1 or 2 contact holders

**GN 651**  
Page 1580



**Features:**

- $l_1$ : 300 / 400 / 500
- With crystal clear plastic indicator tube made from acrylic (PMMA)

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

