



1.1  
1.2  
1.3  
1.4

1 2 3

d <sub>1</sub>		d <sub>2</sub>		l <sub>1</sub>						d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke	l <sub>2</sub>	
14	M 5	M 6		12	16	20	25	32	40	50	10	25	4,5	35	3,5	45
18	M 6	M 8		16	20	25	32	40	50	63	13,5	31	6,5	45	4	62
22	M 10	-		20	25	32	40	50	63	80	16	36	8	52	4	74
25	M 12	-		25	32	40	50	63	80	-	19	43	11	63	4	89
30	M 16	-		32	40	50	63	80	-	-	23	50,5	12	76	5	108

**Specification**

- Handle  
Zinc die casting
- Powder coated  
Black, RAL 9005, textured finish **● SW**  
Orange, RAL 2004 **● OS**
- Threaded stud and retaining screw  
Steel
  - Property class 5.8
  - Blackened
- *Strength Values of Screws* → Page 2152
- RoHS

**On request**

- With inch threads

4

**Information**

Adjustable hand levers GN 101 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever disengages serrations and allowing to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- *Adjustable Hand Levers GN 101.1 (Threaded Stud Stainless Steel)*  
→ Page 455
- *Adjustable Hand Levers GN 300 (Threaded Stud Steel, Blackened)*  
→ Page 429
- *Flat Adjustable Hand Levers GN 302 (Threaded Stud Steel, Blackened)*  
→ Page 449
- *Adjustable Hand Levers GN 300.2 (Threaded Stud, Zinc Plated)*  
→ Page 431
- *Adjustable Hand Levers GN 602.1 (Threaded Stud, Stainless Steel)*  
→ Page 459

2.1  
2.2  
2.3  
2.4

How to order

**GN 101-22-M10-40-SW**

1	d <sub>1</sub>
2	d <sub>2</sub>
3	l <sub>1</sub>
4	Color