

# Clamp mountings

Range









With clamp mountings, tubes and rods can be fixed with better clamping pressure with minimum space requirement. Standardized hole spacings and thread dimensions make the replacement of mounting clamps very simple and efficient during assembly, thanks to the standardized tool.

The large range of clamp mountings enables almost all positioning options. In particular, swivel clamp mountings can be combined to jointed clamp mountings.

The aluminum alloy used for the clamp mountings shows excellent strength and good chemical resistance, and it is permissible for use for foodstuffs. The version with black anodized surface is additionally protected against corrosion and is suitable for applications where reflecting surfaces are not desired. Together with fastening and clamping screws made from corrosion resistant A2 stainless steel use under unfavorable ambient conditions is possible.











Accessories such as sensor plates, retaining rods and tubes as well as clamping kits complete the range. If required, a suitable retaining magnet (GN 51.6 → Page 1395) is available to facilitate rapid repositioning.

Positioning of sensors, scanners, reflectors, cameras, coolant pipes and air nozzles is a typical practical application.

|  |   |  |  |
|--|---|--|--|
| <p><b>Base plate clamp mountings</b><br/>GN 473 → Page 1246</p>        |    | <p><b>Clamp mountings</b><br/>GN 477 → Page 1247</p>                   |    |
| <p><b>Two-way clamp mountings</b><br/>GN 474 → Page 1248</p>           |  | <p><b>Twistable two-way clamp mountings</b><br/>GN 475 → Page 1249</p> |  |
| <p><b>Twistable two-way clamp mountings</b><br/>GN 490 → Page 1255</p> |  | <p><b>T-Clamp mountings</b><br/>GN 476 → Page 1251</p>                 |  |
| <p><b>Two-way clamp mountings</b><br/>GN 474.1 → Page 1249</p>         |  | <p><b>Attachment clamp mountings</b><br/>GN 478 → Page 1252</p>        |  |

# Clamp mountings

Range

|   |   |  |  |                    |
|---|---|--|--|--------------------|
| <p><b>Swivel clamp connector bases</b><br/>GN 485 → Page 1256</p>                     |    | <p><b>Swivel clamp mountings</b><br/>GN 482 → Page 1257</p>                            |    | <p>3.1<br/>3.2</p> |
| <p><b>T-Swivel clamp mountings</b><br/>GN 483 → Page 1258</p>                         |    | <p><b>Attachment clamp mountings</b><br/>GN 484 → Page 1259</p>                        |   | <p>3.3<br/>3.4</p> |
| <p><b>Twistable two-way clamp mountings</b><br/>GN 490 → Page 1255</p>                |    | <p><b>Retaining rods</b><br/><b>Retaining tubes</b><br/>GN 480.1 → Page 1276</p>       |    | <p>3.5<br/>3.6</p> |
| <p><b>Stainless Steel- Retaining rods, angled</b><br/>GN 480.3<br/>→ New products</p> |   | <p><b>Stainless Steel- Retaining rods, cranked</b><br/>GN 480.5<br/>→ New products</p> |   | <p>3.7</p>         |
| <p><b>Stainless Steel- Hose adapters</b><br/>GN 480.7<br/>→ New products</p>          |  | <p><b>Stainless Steel- Thread adapters</b><br/>GN 480.8<br/>→ New products</p>         |  | <p>3.8<br/>3.9</p> |
| <p><b>Stainless Steel- Sensor holders</b><br/>GN 479 → Page 1262</p>                  |  | <p><b>Stainless Steel- Retaining plates</b><br/>GN 479.1 → Page 1263</p>               |  | <p>3.9</p>         |

