


2 Lead direction

RH Right-hand thread



1

d x P Single-start	Length l	A/F
8 x 1,5	12	12
10 x 2	15	17
10 x 3	15	17
12 x 3	18	19
14 x 4	21	22
16 x 4	24	27
18 x 4	27	27
20 x 4	30	30
24 x 5	36	36
30 x 6	45	46
36 x 6	54	55
40 x 7	60	65
50 x 8	75	75

Specification

Steel 1.0718

ST

Stainless steel AISI 303

NI

RoHS

Accessory

GN 103 Trapezoidal Lead Screws

Page

QVX

Trapezoidal lead nuts GN 103.2 are used together with trapezoidal thread spindles GN 103. The wrench flats are used for fastening and prevent the nut from turning. The nut can also be driven via the hexagon.

Since steel and stainless steel nuts tend to cold welding (seizing), the thread must be permanently lubricated. Therefore, steel and stainless steel nuts are primarily used for sporadic adjustments.

see also...

	Page
GN 103.1 Trapezoidal Lead Nuts (Gunmetal, with Flange)	QVX
GN 103.1 Trapezoidal Lead Nuts (Plastic, with flange)	QVX
GN 103.3 Trapezoidal Lead Nuts (Cylindrical)	QVX

Technical Information

Technical Information	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 103 Trapezoidal Lead Screws	QVX
--------------------------------	-----

How to order

GN 103.2-20x4-RH-ST

1	d x P
2	Lead direction
3	Material