




1			2							
d ₁	d ₂		d ₃	h ₁	h ₂	h ₃ ≈	h ₄ Stroke	l ₂	t min.	
14	M 5	M 6	10	25	4,5	35	3,5	45	9	
18	M 6	M 8	13,5	31	6,5	45	4	62	11	
22	M 8	M 10	16	36	8	52	4	74	14	
25	M 10	M 12	19	43	11	63	4	89	17	
30	M 12	M 16	23	50,5	12	76	5	108	22	

Specification

3

Handle

Zinc die casting

Powder coated

• Black, RAL 9005, textured finish

• Orange, RAL 2004, textured finish

● SW

● OS

Insert / Retaining screw

Stainless steel AISI 303

RoHS

Adjustable hand levers GN 101.1 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever disengages serrations and allowing to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...	Page
GN 101 Adjustable Hand Levers (Insert Steel)	QVX
GN 300.1 Adjustable Hand Levers (Insert Stainless Steel)	QVX
GN 300.2 Adjustable Hand Levers (Insert Steel, Zinc plated)	QVX
GN 302.1 Flat Adjustable Hand Levers (Insert Stainless Steel)	QVX
GN 300.5 300.6 Adjustable Hand Levers	QVX
GN 604.1 Adjustable Hand Levers (Handle Plastic)	QVX

Technical Information	
Stainless Steel Characteristics	QVX

How to order

1

2

3

GN 101.1-22-M8-SW

1	d ₁
2	d ₂
3	Color