




b₁	l₁ max. threaded-in	b₂	b₃	d	h₁ ≈	h₂	l₂ ≈	l₃ ≈	l₄	s
25	500	34	22	5,3	11,7	8	250	340	8	1,5
25	700	34	22	5,3	11,7	8	250	540	8	1,5
25	900	34	22	5,3	11,7	8	450	540	8	1,5
25	1050	34	22	5,3	11,7	8	250	890	8	1,5
25	1250	34	22	5,3	11,7	8	450	890	8	1,5
25	1600	34	22	5,3	11,7	8	800	890	8	1,5

Specification

Buckle / Fasteners

Stainless steel AISI 304

NI

Strap

Plastic, polyester

• Woven

• Black

● B

RoHS

Technical Information

ganternorm.com

Application Examples

Plastic Characteristics

2158

Stainless Steel Characteristics

2166

Tension straps GN 1111 are used for securing boxes or crates in holders or fastening containers onto carriers. They consist of two straps and can be screwed or riveted in place with the fittings securely sewn onto the ends.

The straps are connected by threading them into the buckle. The buckle locks the belt in the direction of pull; to release it, the spring-loaded locking pawl must be pressed to raise it up.

Types AD and BD can be quickly and easily attached or detached thanks to the additional hook latch. With these types, the loose strap end is folded over and stitched to prevent the lashing strap from unintentionally working its way out.

Tension straps GN 1111 may not be used for lifting loads or for lashing.

How to order

1

2

3

4

5

GN 1111-25-700-BB-NI-B

1

2

3

4

5

b₁

l₁

Type

Material

Color