



elasa
Original design NSF



2 Lead direction
RH Right-hand thread

1

d ₁ x P Single-start	d ₂	d ₃	d ₄	d ₅	l ₁	l ₂
10 x 2	25	42	34	5	25	10
10 x 3	25	42	34	5	25	10
12 x 3	28	48	38	6	35	12
14 x 4	28	48	38	6	35	12
16 x 4	28	48	38	6	35	12
18 x 4	28	48	38	6	35	12
20 x 4	32	55	45	7	44	12
24 x 5	32	55	45	7	44	12
30 x 6	38	62	50	7	46	14

Specification

- Plastic, Polyamide
- Beige
- Operating temperature -40 °C to +90 °C
- Plastic, Polyacetal
- FDA compliant plastic granulate
- White
- Operating temperature -40 °C to +90 °C
- Plastic Characteristics → Page 2158
- RoHS

3

PA

POM

Accessory

- Trapezoidal Lead Screws GN 103
→ Page XYZ

Information

Trapezoidal lead nuts GN 103.1 are used together with trapezoidal lead screws GN 103. They can be fastened to the component to be adjusted via the bores in the flange.

The trapezoidal lead nuts should be lubricated to minimize wear.

see also...

- Trapezoidal Lead Nuts GN 103.1 (Gunmetal, with Flange) → Page XYZ
- Trapezoidal Lead Nuts GN 103.2 (with Hex) → Page XYZ
- Trapezoidal Lead Nuts GN 103.3 (Cylindrical) → Page XYZ

How to order

GN 103.1-24x5-RH-PA

- 1 d₁ x P
- 2 Lead direction
- 3 Material

