



STAINLESS  
\*\*\*\*

3 Type

- A With 2 key rings
- B With mounting tab and key ring
- C With 2 mounting tabs

Length l			d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	BL	TR	Static load in N ≈	
								with key ring	without key ring
150	200	320	14	1	1,6		3	75	1500
150	200	320	18	1,3	1,6		3	125	1500
150	200	320	24	1,5	1,6		3	140	1500

d <sub>1</sub>	Key rings (Type A and B) suitable for ball lock pins / locking pins with pin Ø											
	GN 113.1 GN 113.3 GN 113.4 GN 113.7 GN 113.8 GN 113.9 GN 113.10	GN 113.5 GN 113.6	GN 113.11 GN 113.12	GN 113.20 Form P	GN 113.20 Form L Form T	GN 114.2 GN 114.3 GN 114.6	GN 114.7 GN 114.8	GN 114.11 GN 114.12	GN 124.1 GN 124.2	GN 124.3	GN 214.2 GN 214.3 GN 214.6	GN 314
14	5...8	5...16	5...10	5	5...6	6...20	6...8	6...12	6...12	8...10	6...8	-
18	10...25	-	12...16	6...12	-	-	10...20	16...20	-	12	10...16	8...12
24	-	-	20...25	-	8...10	-	-	-	-	-	-	16...20

4 Specification

Retaining cable

Stainless steel AISI 316

- Plain finish ○ BL
- Plastic coated (PVC) ○ TR
- Transparent

Mounting tab

Stainless steel AISI 316

Plain finish

Key ring

Stainless steel AISI 316 Ti

Plain finish, tumbled

Press sleeves

Stainless steel AISI 316

RoHS

Technical Information

Stainless Steel Characteristics

Page

QVX

Retaining cables GN 111.8 are available in 3 different types and can therefore be used in a wide range of applications, e.g. for loss protection or as connecting and mounting cables.

Due to the selection of materials, the retaining cables are suitable for use in highly corrosive environments. The coating of version TR protects adjacent parts from chafing or other damage. The smooth surface is also pleasant to the touch.

On delivery the key rings are already mounted on the retaining cable. With type A, both rings have the same diameter d<sub>1</sub>.

The alignment of the cable eyelets and mounting tabs may deviate from the drawing.

The details on static loads are guide values given without warranty.

see also...

GN 111.2 Retaining Cables (Stainless Steel)

Page

QVX

How to order (Type C)

GN 111.8-150-C-BL

- 1 Length l
- 3 Type
- 4 Color

How to order (Type A and B)

GN 111.8-200-18-A-TR

- 1 Length l
- 2 d<sub>1</sub>
- 3 Type
- 4 Color

