
## **Trapezoidal Lead Nuts**


Steel / Stainless Steel / Gunmetal / Plastic, Single- or Multi-Start, Cylindrical








Multi-start thread











#### Lead direction

RH Right-hand thread LH Left-hand thread

### Identification no.

- Short version (Material ST / NI)
- Long version (Material ST / RG / POM)



d <sub>1</sub> x P	$d_2$	Length I		
Single-start		Identification no. 1	Identification no. 2	
8 x 1,5	18	12	16	
10 x 2	22	15	20	
10 x 3	22	15	20	
12 x 3	26	18	24	
14 x 4	30	21	28	
16 x 4	36	24	32	
18 x 4	40	27	36	
20 x 4	45	30	40	
24 x 5	50	36	48	
30 x 6	60	45	60	
36 x 6	75	54	72	
40 x 7	80	60	80	
50 x 8	90	75	100	

V					
d <sub>1</sub> x Ph	d <sub>2</sub>	Length I		P <sub>T</sub>	Number of thread turns
Multi-start		Identification no. 1	Identification no. 2	Pitch	Ph / P <sub>T</sub>
12 x 6*	26	18	24	P3	2
16 x 8*	36	24	32	P4	2
20 x 8*	45	30	40	P4	2
24 x 10*	50	36	48	P5	2
30 x 12*	60	45	60	P6	2
40 x 14*	80	60	80	P7	2

\* For lead direction RH only

# Specification

Steel 1.0718	ST
Stainless steel AISI 303	NI
Gunmetal (Rg7)	RG
Plastic, Polyacetal	POM

White

• Operating temperature up to 90 °C

RoHS (only ST / NI and POM)

Technical Information	Page
Technical Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Trapezoidal lead nuts GN 103.3 are used together with trapezoidal lead screws GN 103. The nuts are available in various lengths depending on the material and the resulting strength. The nuts can be fastened via individually machined surfaces, grooves or threads on the flat surfaces or on the circumference.

To minimize wear, the trapezoidal lead nuts should be lubricated. However, if lubrication is insufficient, the bronze alloy (gunmetal) generally has emergency running properties. Steel and stainless steel nuts are primarily used for sporadic adjustments.

see also	Page
GN 103.1 Trapezoidal Lead Nuts (Gunmetal, with Flange)	QVX

#### Accessory

How to order

GN 103.3-24x10-RH-1-ST

4

GN 103 Trapezoidal Lead Screws QVX

1	$d_1 \times Ph (d_1 \times P)$
2	Туре
3	Identification no.
4	Material

က်

5 3