



1

2

l_1	d H7 Blind bore		b	h_1	h_2	$h_3 \approx$	l_2	t min.	\varnothing Handle
70	S 8	-	17	19	11,5	42,5	26,5	12	18
80	S 8	-	18	21	12,5	52,5	31	12	21
90	S 10	-	19	23	13,5	52,5	35,5	15	21
100	S 10	S 12	20	25	14	67,5	40	17	23

Specification

- Body
Zinc die casting
Powder coated
Black, textured finish
- Revolving handles GN 598
 - Plastic, Technopolymer
Black, matte finish
 - Spindle steel
Zinc plated, blue passivated
- ISO Fundamental Tolerances → Page 2151
- RoHS

Information

Control handles GN 112.1 allow fine adjustment.

They are connected to a shaft by means of a cross pin. To simplify the installation there is a centred drilling on both sides.

see also...

- Cranked Handles GN 510 (Plastic) → Page 297

How to order

GN 112.1-90-S10

1 l_1

2 d