


- 1 Type
- SG With star knob  
KGN With wing knob  
HGN With lever  
SKN With wing knob  
STN With T-handle
- 3 Version of the hook
- H1 Pivoting radius R=28
- 5 Identification no.
- 1 Without latch bracket  
2 With latch bracket



Hook distance A	d		h	
	Type SG / KGN / HGN	Type SKN / STN	Type SG / KGN / HGN	Type SKN / STN
18	28	32	4	6

\* Dimensions of the latch bracket → Page XYZ

Specification

Lock housing

Stainless steel

• AISI 303 for type SG / KGN / HGN  
• AISI 316 for type SKN / STN

Operating element

• Stainless steel AISI 304 for type SG  
Sheet metal drawn / Hub welded  
• Stainless steel AISI CF-8 for type KGN / HGN  
• Stainless steel AISI 316 for type SKN / STN

Other parts

Stainless steel AISI 304

RoHS

On request

• Hook-type latches with other hook distance A  
• Hook with other pivoting radius R

Hook-type latches GN 115.8 with hook and catch are mainly used for sliding doors and flaps. The locking action is in radial direction to the axis of rotation, resulting in a wide variety of different uses. The hook-type latches GN 115.8 are supplied with loosely enclosed hook.

see also...	Page
GN 115.8 Hook-Type Latches (Zinc Die Casting, with Operating Element)	QVX
Technical Information	
Construction and assembly instructions	QVX
Overview Latch Types	QVX
Stainless Steel Characteristics	QVX

How to order

1 Type  
2 Hook distance A  
3 Version of the hook  
4 Material  
5 Identification no.

GN 115.8-HGN-18-H1-N-1