



- 1 Type
- RG With knurled knob  
GN 7336
- KG With wing knob
- HG With lever

2

Latch arm distance A														
6	10	14	18	20	22	24	26	28	30	34	38	40	50	

3

Specification	
• Lock housing	NI
Stainless steel AISI 303	
• Latch arm	
Stainless steel AISI 304	
• Operating elements	
Plastic (Polyamide PA)	
Black, matte finish	
• Other parts	
Stainless steel AISI 304	
• Protection class IP 65	
• IP Protection Classes → Page 2153	
• Plastic Characteristics → Page 2158	
• Stainless Steel Characteristics → Page 2166	
• RoHS	

Accessory	
• Protective Guide Plates GN 120.2	→ Page 1270
• Internal Cabinet Handles GN 120.3	→ Page XYZ
• Sheet Metal Punches GN 123	→ Page 1267

Information	
Latches GN 115 are locked by a rotation limited to 90°, which moves the latch arm into the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments.	
Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.	
Latches GN 115 are supplied with loosely enclosed latch arm.	
see also...	
• Construction and Assembly Instructions → Page 1201	
• List of Latch Types → Page 1196 ff.	
• Latches GN 115 (Steel, Zinc Plated, with Operating Elements) → Page 1200	
• Latches GN 115 (Stainless Steel, with Operating Elements in Stainless Steel) → Page XYZ	
• Latches GN 115 (Stainless Steel A4, with Operating Elements) → Page XYZ	
• Latches GN 115 (Stainless Steel, Lockable) → Page 1208	
How to order	
1 Type	2 Latch arm distance A
3 Material	