



- 1 Type**
- SG** With star knob
 - KGN** With wing knob
 - HGN** With lever
 - SKN** With wing knob
 - STN** With T-handle

2

Latch arm distance A											d	h					
											Type SG, HGN, KGN	Type SKN, STN	Type SG, HGN, KGN	Type SKN, STN			
6	10	14	18	20	22	24	26	28	30	34	38	40	50	28	32	4	6

Specification

- Lock housing
 - Type SG, KGN, HGN
Stainless steel AISI 303
 - Type SKN, STN
Stainless steel AISI 316
- Latch arm
Stainless steel AISI 304
- Operating elements
 - Type SG
Stainless steel AISI 304
Sheet metal drawn and hub welded
 - Type KGN, HGN
Stainless steel AISI CF-8
 - Type SKN, STN
Stainless steel AISI 316
- Other parts
Stainless steel AISI 304
- Protection class IP 65
- IP Protection Classes → Page 2153
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

3

Information

Latches GN 115 are locked by a rotation limited to 90°, which moves the latch arm into the locked position behind the door frame. The bevels of the latch arm ease the closing of the door.

Thanks to the stainless steel material, the latches are optimally suited for use in highly corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.

Latches GN 115 are supplied with loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → Page 1201
- List of Latch Types → Page 1196 ff.
- Latches GN 115 (Steel, Zinc Plated, with Operating Elements) → Page 1200
- Latches GN 115 (Stainless Steel A4, with Operating Elements) → Page XYZ
- Latches GN 115 (Stainless Steel, Lockable) → Page 1208

How to order

GN 115-SG-18-NI

1	Type
2	Latch arm distance A
3	Material