




2

Latch distance A								
6	10	14	18	20	22	24	26	28

3

Specification	
Lock housing / Operating elements	A4
Stainless steel AISI 316	
Latch	
Stainless steel AISI 316	
Other parts	
Stainless steel AISI 316	
Protection class IP 65	
RoHS	

Latches GN 115 are locked by a rotation limited to 90°, which moves the latch arm into the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Thanks to the stainless steel material, the latches are optimally suited for use in highly corrosive environments. Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 28 mm. Latches GN 115 are supplied with loosely enclosed latch arm.

see also...	Page
GN 115 Latches (Stainless Steel, with Operating Elements)	QVX
GN 115 Latches (Stainless Steel, with Plastic Operating Elements)	QVX
GN 115 Latches (Stainless Steel, Operation with Socket Keys, Protection Class IP 69k)	QVX
GN 115 Latches (Stainless Steel, Lockable)	QVX

Technical Information	
Construction and Assembly Instructions	QVX
Overview of Latch Types	QVX
IP Protection classes	QVX
Stainless Steel Characteristics	QVX

Accessory	
GN 120.4 Electromechanical Locking Systems	QVX
GN 123 Sheet Metal Punches	QVX
GN 120.2 Protective Guide Plates	ganternorm.com
GN 120.3 Internal Handles	ganternorm.com

How to order	
1	Type
2	Latch distance A
3	Material
GN 115-SKN-10-A4	