



- Type**
- SG** With star knob
 - SK** With wing knob
 - ST** With T-handle
 - RG** With knurled knob
GN 7336
 - KG** With wing knob
 - HG** With lever
 - LG** With hand lever
(only in SW)

2

Latch arm distance A											d		h	
4	8	13	16	20	24	28	32	36	40	45	Type SG, RG, KG, HG	Type SK, ST, LG	Type SG, RG, KG, HG	Type SK, ST, LG
4	8	13	16	20	24	28	32	36	40	45	28	32	4	6
6	10	14	18	22	26	30	34	38	42	50	28	32	4	6

Specification

- Lock housing
Zinc die casting
 - Housing collar, chrome plated —
 - Housing collar, powder coated Black, RAL 9005, textured finish ● **SW**
- Operating elements
 - Type SG, SK, ST, RG, KG, HG
Plastic (Polyamide PA)
Black, matte finish
 - Type LG
Zinc die casting
Powder coated
Black, RAL 9005, textured finish
- Cover cap (Type RG, KG, HG, LG)
Plastic (Polyamide PA)
Light gray, matte finish
- Other parts
Steel, zinc plated, blue passivated
- Protection class IP65
- IP Protection Classes → Page QVX
- RoHS

3

Information

Latches GN 115 lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door.

Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 50 mm.

Latches GN 115 are supplied with loosely enclosed latch arm.

see also...

- List of Latch Types → Page 1196 ff.
- Latches GN 115 (Operation with socket key) → Page 1202
- Latches GN 115 (Lockable) → Page 1203
- Latches GN 115 (Stainless Steel) → Page 1206 ff.

How to order (Housing collar, chrome plated)

1	Type
2	Latch arm distance A

GN 115-SG-20

How to order (Housing collar, black)

1	Type
2	Latch arm distance A
3	Finish

GN 115-HG-32-SW