




Latch distance A													
6	10	14	18	20	22	24	26	28	30	34	38	40	50

Specification

Lock housing	NI
Stainless steel	
AISI 303	
Latch	
Stainless steel AISI 304	
Operating element	
Plastic (Polyamide PA)	
Black, matte finish	
Other parts	
Stainless steel AISI 304	
Protection class IP 65	
RoHS	

Latches GN 115 lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments. Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm. Latches GN 115 are supplied with loosely enclosed latch arm.

see also...	Page
GN 115 Latches (Steel, Zinc Plated, Operation with Operating Elements)	QVX
GN 115 Latches (Stainless Steel, with Operating Elements)	QVX
GN 115 Latches (Stainless Steel AISI 316, with Operating Elements)	QVX
GN 115 Latches (Stainless Steel, Lockable)	QVX

Technical Information

Construction and Assembly Instructions	QVX
Overview of Latch Types	QVX
IP Protection classes	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 120.4 Electromechanical Locking Systems	QVX
GN 123 Sheet Metal Punches	QVX
GN 120.2 Protective Guide Plates	ganternorm.com
GN 120.3 Internal Handles	ganternorm.com

How to order	1 Type
GN 115-RG-28-NI	2 Latch distance A
	3 Material