



Type **DK6,5**
Type **DK7**




Type **VK6**
Type **VK7**
Type **VK8**



Type **VDE5**



Type **SCH**



2 Type

- DK6,5** With triangle $h = 6,5$
- DK7** With triangle $h = 7$
- VK6** With square $A/F6$
- VK7** With square $A/F7$
- VK8** With square $A/F8$
- VDE5** With double bit $d_2 = 5,6$
- SCH** With blade / slot

1

l_1	l_2	b	d_1	d_2	h	s	A/F	Type					for latches			
55	34	32	11,4	-	6,5	1,3	6	DK6,5	VK6	-	SCH					GN 115.1 / GN 115.6
86	53	50	14	5,6	7	1,8	7	DK7	VK7	VDE5	SCH					GN 115 / GN 115.7 / GN 115.8 / GN 115.10 / GN 116.1 / GN 119 GN 119.3 / GN 515 / GN 516 / GN 516.1 / GN 516.5
86	53	50	14	-	-	-	8	-	VK8	-	-					GN 115 / GN 115.7 / GN 115.8 / GN 115.10 / GN 116.1 / GN 119 GN 119.3 / GN 515 / GN 516 / GN 516.1 / GN 516.5

Specification

3

- Zinc die casting
- Powder coated
- Black, textured finish



- RoHS

How to order

GN 119.2-86-VK8-SW

- 1** l_1
- 2** Type
- 3** Finish