



elasa
Original design CFP. / CFQ.

- 3 Type**
- SH** 2x2 bores for countersunk screws
 - CH** 2x2 bores for socket cap screws
 - EH** 2x2 bores for hexagon screws

| 1 l_1 | 2 l_2 | l_3 | d_1 | d_2 | h_1 | h_2 | h_3 | m_1 | m_2 | t_1 | t_2 | Max. holding torque M_H in Nm |
|----------------|----------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|---------------------------------|
| 45 | 50 | 21,5 | 4,5 | 8 | 14 | 8 | 7 | 25 | 32 | 4,5 | 4,5 | 1,1 |

Specification

- Plastic (Polyacetal POM)
 - Glass fiber reinforced
 - Black, matte finish
 - Temperature resistant up to 80 °C
- *Load Rating Information* → Page 2126
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

Hinges GN 122.1 with indexing positions keep the door in the three specified positions without additional mechanism.

Hinges GN 122.2 are free running having the same design as hinges GN 122.1.

The covers prevent not only the entering of dirt in the range of the screws, but give as well an appealing appearance to the hinges.

see also...

- *List of Hinge Types* → Page 1284 ff.

| | |
|--|----------------|
| How to order (With indexing positions) | 1 l_1 |
| | 2 l_2 |
| GN 122.1-45-50-SH | 3 Type |

| | |
|---|----------------|
| How to order (Without indexing positions) | 1 l_1 |
| | 2 l_2 |
| GN 122.2-45-50-SH | 3 Type |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9