



3 Type

- D** Straight lever
- E** Angled lever

1 **2**

| d ₁ | d ₂ | d ₃ | d ₄ | d ₅ | h ₁ | h ₂ | h ₃ | h ₄ ≈ | h ₅ Stroke | l | t min. |
|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|------------------|--------------------------|-----|-----------|
| 32 | M 6 M 8 | 13,5 | 8 | 20 | 20,5 | 1,5 | 12,5 | 36 | 4 | 100 | 11 |
| 36 | M 8 M 10 | 16 | 10 | 25 | 24,5 | 2 | 15 | 45 | 4,5 | 120 | 14 |
| 40 | M 10 M 12 | 19 | 12 | 30 | 30 | 4 | 19 | 53 | 4,5 | 130 | 17 |
| 45 | M 12 M 16 | 23 | 12 | 32 | 35,5 | 4 | 24 | 64 | 5 | 145 | 23 |

Specification

- Stainless steel AISI 303
Matte shot-blasted
- Cover
Plastic, light gray
- Ball knobs DIN 319
Plastic, Duroplast
Black, shiny finish
- Safety circlip
Plastic (Polyacetal)
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

On request

- With threaded through hole
- With inch threads

Information

The overall height of flat adjustable stainless steel tension levers GN 125.5 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

- *Flat Adjustable Tension Levers GN 125 (Steel, Blackened)* → Page 484
- *Flat Adjustable Tension Levers GN 126.1 (Bushing Stainless Steel)*
→ Page 488

How to order

GN 125.5-40-M12-E

- 1** d₁
- 2** d₂
- 4** Type