



3 Type

- D** Straight lever
- E** Angled lever

1 **2**

d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈	h ₅ Stroke	l	t min.	
32	M 6	M 8	-	13,5	8	20	20,5	1,5	12,5	36	4	100	11
36	M 8	M 10	M 12	16	10	25	24,5	2	15	45	4,5	120	14
40	M 10	M 12	-	19	12	30	26,5	2	16	50	4,5	130	17
45	M 12	M 14	M 16	23	12	32	31,5	2	20	60	5	145	23

Specification

- Steel
Blackened
- Cover
Plastic, light gray
- Ball knobs DIN 319
Plastic, Duroplast
Black, shiny finish
- Safety circlip
Plastic (Polyacetal)
- *Plastic Characteristics* → Page 2158
- **RoHS**

On request

- With threaded through hole
- With inch threads

Information

The overall height of flat adjustable tension levers GN 125 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

- *Flat Adjustable Stainless Steel Tension Levers GN 125.5* → Page 486
- *Adjustable Flat Tension Levers GN 126 (Bushing, Steel)* → Page 488

How to order

GN 125-32-M8-D

- 1** d₁
- 2** d₂
- 4** Type