



**4 Type**

- D** Straight lever
- E** Angled lever

1 2 3

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>					d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> ≈	h <sub>5</sub> Stroke	l <sub>2</sub>			
32	M 8	12	16	20	25	32	40	50	-	13,5	8	20	20,5	1,5	12,5	36	4	100
36	M 10	16	20	25	32	40	50	63	80	16	10	25	24,5	2	15	45	4,5	120
40	M 12	25	32	40	50	63	80	-	-	19	12	30	30	4	19	53	4,5	130
45	M 16	32	40	50	63	80	-	-	-	23	12	32	35,5	4	24	64	5	145

**Specification**

- Stainless steel AISI 303  
Matte shot-blasted
- Cover  
Plastic, light gray
- Ball knobs DIN 319  
Plastic, Duroplast  
Black, shiny finish
- Safety circlip  
Plastic (Polyacetal)
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**On request**

- With inch threads

**Information**

The overall height of flat adjustable stainless steel tension levers GN 125.5 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

**see also...**

- *Flat Adjustable Tension Levers GN 125 (Steel, Blackened)* → Page 485
- *Flat Adjustable Tension Levers GN 126.1 (Threaded Stud Stainless Steel)* → Page 489

**How to order**

**GN 125.5-32-M8-20-D**

- 1 d<sub>1</sub>
- 2 d<sub>2</sub>
- 3 l<sub>1</sub>
- 4 Type