



- 4 Type**
- H** Vertically adjustable
  - B** Horizontally adjustable
  - HB** Vertically and horizontally adjustable

**Operating principle**






**Swiveling range**



Type H

Type B

Type HB



l <sub>1</sub>	l <sub>2</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>3</sub>	m <sub>1</sub>	m <sub>2</sub>	w	Adjustable range	
											x	Material ZD
52	40	4,5	4	9,5	6	5,5	22	30	22	2	0,5	1
64	50	5,5	6	11,5	7	6,5	28	37	27	3	0,75	1,5
76	60	6,5	8	15	9	8,5	33,5	42	34	4	1	2

**Specification**

- Zinc die casting **ZD**
- Powder coated
- Black, RAL 9005, textured finish **● SW**
- Silver, RAL 9006, textured finish **● SR**
- Stainless steel AISI 316 **A4**
- Matte shot-blasted **GS**
- Pin
- Stainless steel AISI 316Ti
- Load Rating Information → Page 2121
- Stainless Steel Characteristics → Page 2166
- RoHS

**Information**

With hinges GN 127 doors and covers can be positioned snugly and in a finely adjusted manner by moving the adjusting bushings. In this way, door gaps can be readjusted and manufacturing tolerances can be compensated. The arrowheads mark the middle of the adjustable range w.

The Stainless Steel variants are also generally suited for applications under especially aggressive conditions.

- see also...
- List of Hinge Types → Page 1284 ff.

How to order	
1	Material
2	l <sub>1</sub>
3	l <sub>2</sub>
4	Type
5	Finish

**GN 127-ZD-64-50-HB-SR**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9